



KINTEK SOLUTION

Homogenizer 카탈로그

Contact us for more catalogs of [Sample Preparation](#), [Thermal Equipment](#), [Lab Consumables & Materials](#), [Bio-Chem Equipment](#), 등

KINTEK SOLUTION

?? ???

>>> ?? ??

KinTek Group Limited is one technology orientated organization, team members are devoted to probing the most efficient and reliable technology and innovations in the scientific researching equipment, fields like biochemical reacting, new materials researching, heat treatment, vacuum creating, refrigerating, as well as pharmaceutical and petroleum extracting equipment.



제약 및 화장품 응용 분야를 위한 고전단 균질기

품목 번호: COA-7



소개

정밀하고 안정적인 샘플 처리를 위한 고속 실험실 유화 균질기로 실험실 효율성을 향상시키십시오. 제약 및 화장품에 이상적입니다.

자세히 알아보기

매개변수	사양
모델	KT200-S
디스플레이	LED 디지털 튜브
속도 범위	Φ12 & Φ18 헤드: 300 - 20,000 rpm
최대 처리량 (H ₂ O)	300 ml
리프팅 메커니즘	수동
리프팅 스트로크	170 mm
모터 유형	카본 브러시 모터
전원 공급 장치	AC 220V / 50Hz
전력	220 W
순중량	7.5 kg
치수 (L×W×H)	210 × 290 × 330 mm

매개변수	사양
모델	KT-HET-25D
속도 범위	Φ25: 5,000 - 20,000 rpm (H ₂ O 부하 시)
속도 제어	무단계 (노브)
타이머 범위	1 - 8 분
처리량 (H ₂ O)	Φ25: 7,000 ml
최대 처리 점도	Φ25: 3,500 mPa·s
작업 헤드 치수 (Φ×L)	Φ25 × 216 mm
작업 헤드 침지 깊이	62 - 147 mm
작업 헤드 재질	SUS316L

매개변수	사양
전원 공급 장치	AC 220V 50Hz
전력	450 W
순중량	9.54 kg
치수 (L×W×H)	320 × 220 × 630 mm

매개변수	사양
모델	KT-HEA-36
속도 범위	Φ36: 8,000 - 24,000 rpm
속도 제어	무단계 (6단 다이얼)
처리량 범위 (HzO)	Φ36: 500 - 8,000 ml
최대 처리 점도	Φ36: 10,000 mPa·s
작업 헤드 치수 (Φ×L)	Φ36 × 225 mm
작업 헤드 침지 깊이	150 mm
작업 헤드 재질	316 스테인리스 스틸
전원 공급 장치	AC 160 - 250V 50Hz
전력	1,300 W
순중량	7.85 kg
치수 (L×W×H)	315 × 200 × 670 mm

매개변수	사양
모델	KT-HET-25DT
속도 제어	무단계 (노브)
처리량 (HzO)	Φ25: 7,000 ml
최대 처리 점도	Φ25: 3,500 mPa·s
작업 헤드 치수 (Φ×L)	Φ25 × 216 mm
작업 헤드 침지 깊이	62 - 147 mm
작업 헤드 재질	SUS316L
온도 측정 범위	-10 ~ 200°C
전원 공급 장치	AC 220V 50Hz
전력	1,050 W
순중량	10.5 kg
치수 (L×W×H)	360 × 380 × 638 mm

제약, 화장품 및 식품 R&D용 고성능 실험실 균질기

품목 번호: KT-VHE



소개

제약, 화장품 및 식품용 실험실 진공 균질 유화기. 고전단 혼합, 진공 탈기, 확장 가능한 1L-10L. 지금 전문가와 상담하세요!

[자세히 알아보기](#)

매개변수	KT-VHE-1	KT-VHE-2	KT-VHE-5	KT-VHE-10
교반 부피	100-1000ml	100-2000ml	500-5000ml	1000-10000ml
교반 속도 범위	0-230rpm	0-230rpm	0-230rpm	0-230rpm
교반 패들 스타일	PTFE 벽 스크래퍼가 있는 SUS316L 앵커 타입			
처리 점도	100000CP	100000CP	100000CP	150000CP
교반 동력	120W	150W	150W	300W
유화 부피	500-1000ml	600-2000ml	2500-5000ml	5000-10000ml
균질 속도 범위	8000-28000rpm	8000-28000rpm	8000-30000rpm	8000-30000rpm
균질기 헤드 모델	20DG	25DG	25DG	25DG
균질기 동력	1300W	1300W	1300W	1300W
반응기 뚜껑 포트	교반, 진공, 균질기, 공급, 온도 프로브 + 예비 포트 3개			
리프팅 스트로크	300mm	300mm	500mm	500mm
최대 작동 온도	120°C	120°C	120°C	120°C
달성 가능한 진공	-0.098MPa	-0.098MPa	-0.098MPa	-0.098MPa
전원 공급 장치	AC220V 50Hz	AC220V 50Hz	AC220V 50Hz	AC220V 50Hz
순 중량	35kg	40kg	50kg	55kg
치수 (L×W×H)	400×650×1100 mm	400×650×1100 mm	600×450×1100 mm	600×480×1200 mm

매개변수	KT-VHE-1S	KT-VHE-2S	KT-VHE-5S	KT-VHE-10S
교반 부피	100-1000ml	100-2000ml	500-5000ml	1000-10000ml
교반 속도 범위	0-230rpm	0-230rpm	0-230rpm	0-230rpm
교반 패들 스타일	PTFE 벽 스크래퍼가 있는 SUS316L 앵커 타입			
처리 점도	100000CP	100000CP	100000CP	150000CP

매개변수	KT-VHE-1S	KT-VHE-2S	KT-VHE-5S	KT-VHE-10S
교반 동력	120W	150W	150W	300W
유량 부피	500-1000ml	600-2000ml	2500-5000ml	5000-10000ml
균질 속도 범위	8000-28000rpm	8000-28000rpm	8000-30000rpm	8000-30000rpm
균질기 헤드 모델	20DG	25DG	25DG	25DG
균질기 동력	1300W	1300W	1300W	1300W
반응기 재질	316L 스테인리스 스틸			
반응기 뚜껑 포트	교반, 진공, 균질기, 공급, 온도 프로브 + 예비 포트 3개			
리프팅 스트로크	300mm	300mm	500mm	500mm
최대 작동 온도	120°C	120°C	120°C	120°C
달성 가능한 진공	-0.098MPa	-0.098MPa	-0.098MPa	-0.098MPa
전원 공급 장치	AC220V 50Hz	AC220V 50Hz	AC220V 50Hz	AC220V 50Hz
순 중량	35kg	40kg	50kg	55kg
치수 (L×W×H)	400×650×1100 mm	400×650×1100 mm	600×450×1100 mm	600×480×1200 mm



Kintek Solution

Head Quarter: No.89 Science Avenue, High-Tech Zone,
Zhengzhou, China

