

# Mesh Belt Controlled Atmosphere Furnace

Item Number: KT-MB



## Introduction

Discover our KT-MB mesh belt sintering furnace - perfect for high-temperature sintering of electronic components & glass insulators. Available for open air or controlled atmosphere environments.

[Learn More](#)

Model	KT-MB20	KT-MB30	KT-MB35	KT-MB60	KT-MB65
Working temperature	RT-1000°C				
Control accuracy	±1°C				
Heating element	FEC heater				
Mesh belt width	200mm	300mm	350mm	600mm	650mm
Effective height	50mm	60mm	80mm	80mm	80mm
Hot zone quantity	7	7	8	9	12
Overall length	7200mm	7200mm	7200mm	7650mm	13380mm
Customer design sizes and requirement is accepted					