

Vacuum Induction Melting Spinning System Arc Melting Furnace

Item Number: KT-VIS



Introduction

Develop metastable materials with ease using our Vacuum Melt Spinning System. Ideal for research and experimental work with amorphous and microcrystalline materials. Order now for effective results.

[Learn More](#)

Model	KT-VIS2	KT-VIS15	KT-VIS50	KT-VIS100
Capacity	20g	150g	500g	1000g
Crucible	Boron Nitride/Quartz			
Belt width	1-10mm	1-30mm	1-40mm	1-70mm
Spinner size	φ200mm	φ220mm	φ300mm	φ300mm
Speed	3000r/min			
Vacuum	6.7*10 ⁻⁴ pa			
Insert gas	Ar			
Rated power	7kw	15kw	25kw	35kw
Power supply	AC110-480V 50/60HZ			
Optional part	Infrared temperature meter, recirculating chiller, Spray casting copper mold			

Other requirement can be customized