



KINTEK SOLUTION

Alumina Crucible Catalog

Contact us for more catalogs of [Sample Preparation](#), [Thermal Equipment](#), [Lab Consumables & Materials](#), [Bio-Chem Equipment](#), etc...

KINTEK SOLUTION

COMPANY PROFILE

>>> About Us

Kintek Solution Ltd is one technology orientated organization, team members are devoted to probing the most efficient and reliable technology and innovations in the scientific researching equipment, fields like biochemical reacting, new materials researching, heat treatment, vacuum creating, refrigerating, as well as pharmaceutical and petroleum extracting equipment.

In the past 20 years, we earned rich experiences in this researching equipment field, we are capable to supply both the equipment and solution according to customer's needs and realities, we have also developed lots of customer tailored equipment according to a specific working purpose, and we have lots of successful projects in many universities and institutes from different countries, like Asia, Europe, North and South America, Australia and New Zealand, Middle East, and Africa.

Profession, quick response, hard working, and sincerity is a remarkable label of our team members working attitude, which earn us a sound reputation among our clients.

We are here and ready to service our clients from different countries and regions, and share the most efficient and reliable technology together!



Alumina (Al₂O₃) Crucible With Lid Cylindrical Laboratory Crucible

Item Number: KM-C02



Introduction

Cylindrical Crucibles Cylindrical crucibles are one of the most common crucible shapes, suitable for melting and processing a wide variety of materials, and are easy to handle and clean.

[Learn More](#)

0.4ml(φ10x10mm)	4ml(φ14x45mm)	23ml(φ30x55mm)	74ml(φ45x65mm)	150ml(φ90x30mm)	260ml(φ75x65mm)	470ml(φ80x120mm)	1400ml(φ130x130mm)
0.8ml(φ12x12mm)	6.5ml(φ19x35mm)	25ml(φ28x58mm)	85ml(φ50x60mm)	160ml(φ65x65mm)	275ml(φ60x120mm)	480ml(φ95x95mm)	1600ml(φ140x140mm)
1.5ml(φ20x10mm)	7ml(φ30x20mm)	28ml(φ50x25mm)	89ml(φ60x40mm)	198ml(φ85x50mm)	280ml(φ80x80mm)	560ml(φ130x60mm)	2000ml(φ150x140mm)
3ml (φ12x40mm)	7.5ml(φ28x17mm)	35ml(φ40x40mm)	93ml(φ40x100mm)	220ml(φ60x100mm)	300ml(φ90x65mm)	630ml(φ100x100mm)	2400ml(φ230x80mm)
3ml(φ16x20mm)	9ml(φ30x25mm)	38ml(φ35x51mm)	120ml(φ50x80mm)	220ml(φ70x70mm)	310ml(φ70x100mm)	840ml(φ150x65mm)	2500ml(φ150x180mm)
3ml(φ20x20mm)	12ml(φ30x28mm)	40ml(φ50x30mm)	130ml(φ60x60mm)	220ml(φ100x35mm)	330ml(φ95x60mm)	1000ml(φ115x130mm)	2520ml(φ200x100mm)
3.5ml(φ16x28mm)	13ml(φ30x30mm)	63ml(φ50x45mm)	130ml(φ70x50mm)	250ml(φ85x60mm)	360ml(φ80x100mm)	1100ml(φ100x180mm)	2700ml(φ160x160mm)
3.5ml(φ18x26mm)	21ml(φ35x30mm)	70ml(φ50x50mm)	145ml(φ50x100mm)	250ml(φ95x50mm)	450ml(φ90x90mm)	1350ml(φ125x150mm)	3400ml(φ180x170mm)
5240ml(φ200x200mm)							
0.8mlWith convex cover(φ12x12)	3.5mlWith convex cover(φ16x28)	11mlWith convex cover(φ19x58)	28mlWith buckle cover(φ50x25)	53mlWith convex cover(φ40x70)	100mlwith disc cover(φ58x60)	280mlwith disc cover(φ80x80)	1100mlwith disc cover(φ100x180)
1.5mlWith buckle cover(φ20x10)	3.5mlWith buckle cover(φ16x28)	12mlWith convex cover(φ30x28)	29mlWith convex cover(φ40x35)	61mlWith convex cover(φ40x80)	120mlWith convex cover(φ50x80)	280mlWith buckle cover(φ80x80)	1350mlwith disc cover(φ125x150)
1.5mlWith convex cover(φ20x10)	3.5mlWith convex cover(φ18x26)	12mlWith buckle cover(φ30x28)	35mlWith convex cover(φ40x40)	63mlWith convex cover(φ50x45)	130mlwith disc cover(φ60x60)	300mlWith buckle cover(φ90x65)	1400mlwith disc cover(φ130x130)
3mlWith convex cover(φ12x40)	4mlWith convex cover(φ14x45)	13mlWith convex cover(φ30x30)	38mlWith convex cover(φ35x50)	63mlWith buckle cover(φ50x45)	130mlwith disc cover(φ70x50)	450mlwith disc cover(φ90x90)	1600mlwith disc cover(φ140x140)
2mlWith convex cover(φ16x20)	6.5mlWith convex cover(φ19x35)	13mlWith buckle cover(φ30x30)	38mlWith buckle cover(φ35x50)	70mlWith convex cover(φ50x50)	150mlwith disc cover(φ90x30)	450mlWith buckle cover(φ90x90)	2000mlwith disc cover(φ150x140)
2mlWith buckle cover(φ16x20)	7mlWith convex cover(φ30x20)	15mlWith convex cover(φ47x13)	40mlWith convex cover(φ50x30)	70mlWith buckle cover(φ50x50)	150mlWith buckle cover(φ90x30)	560mlwith disc cover(φ130x60)	2400mlwith disc cover(φ230x80)
3mlWith buckle cover(φ20x18)	7.5mlWith convex cover(φ28x17)	23mlWith convex cover(φ30x55)	50mlWith buckle cover(φ35x70)	73mlWith convex cover(φ35x100)	160mlwith disc cover(φ65x65)	630mlwith disc cover(φ100x100)	2500mlwith disc cover(φ150x180)
3mlWith convex cover(φ20x18)	8mlWith buckle cover(φ25x25)	23mlWith buckle cover(φ30x55)	50mlWith convex cover(φ40x60)	85mlWith convex cover(φ50x60)	163mlwith disc cover(φ90x35)	840mlwith disc cover(φ150x65)	2700mlwith disc cover(φ160x160)
3mlWith convex cover(φ20x20)	9mlWith convex cover(φ20x50)	25mlWith convex cover(φ28x58)	52mlWith buckle cover(φ30x100)	85mlWith buckle cover(φ50x60)	220mlwith disc cover(φ60x100)	950mlwith disc cover(φ120x120)	3400mlwith disc cover(φ180x170)
3mlWith buckle cover(φ20x20)	9mlWith convex cover(φ30x25)	28mlWith convex cover(φ50x25)	52mlWith convex cover(φ30x100)	95mlwith disc cover(φ95x20)	260mlwith disc cover(φ70x70)	1000mlwith disc cover(φ115x130)	

0.4ml(10x10)	1.5ml(13x24)	3ml(20x18)	5ml(15x70)	8ml(25x25)	15ml(30x28)	39ml(35x58)
0.7ml(20x4)	2ml(30x5)	3ml(35x6)	6ml(16x50)	9ml(20x50)	15ml(47x13)	50ml(35x70)
1ml(10x50)	2.5ml(10x60)	4ml(12x150)	6.5ml(19x35)	11ml(19x58)	18ml(23x60)	50ml(40x60)
1.2ml(11x20)	3ml(12x40)	4ml(14x45)	8ml(16x56)	12ml(55x8)	29ml(40x35)	

One large (φ58x60) and seven small (φ16x50)	One large (100x40x20) and three small (φ28x17)	One large (120x60x20) two small (100x20x20 semicircle)
One large (φ70x70) and three small (φ28x58)	One large (100x40x20) and three small (φ30x30)	One large (120x60x40) three small (40x35x25 semicircle)
One large (100x30x20) and four small (φ20x20)	One large (100x100x40) nine small (10ml)	One large (120x80x30) six small (20ml)
One big (100x30x20) five small (φ18x26)	One large (115x65x45) four small (50x25x35)	One large (120x80x40) six small (15ml)

52ml(30x100)	80ml(56x50)	119ml(40x135)	180ml(50x120)	270ml(90x60)
53ml(40x70)	95ml(95x20)	127ml(45x110)	185ml(59x87)	300ml(100x50)
61ml(40x80)	100ml(58x60)	140ml(115x20)	230ml(100x40)	375ml(70x120)
73ml(35x100)	105ml(75x27)	163ml(90x35)	250ml(70x90)	420ml(70x145)

2mlwith outer buckle cap(φ16x20)	6mlwith inner convex cap(φ16x50)	220ml with disc cover (φ100x35)	300ml with disc cover (φ100x50)	610ml with disc cover (φ80x155)	900ml with disc cover (φ115x110)
2mlwith inner convex cap(φ16x20)	8mlwith buckle cap(φ16x56)	250ml with disc cover (φ85x60)	330ml with disc cover (φ95x60)	610mlwith buckle cap(φ80x155)	1050ml with disc cover (φ150x80)
3.5mlwith buckle cap(φ16x28)	8mlwith inner convex cap(φ16x56)	250mlwith buckle cap(φ85x60)	360ml with disc cover (φ80x100)	790ml with disc cover (φ80x200)	1100ml with disc cover (φ100x180)
3.5mlwith inner convex cap(φ16x28)	50ml with disc cover (φ40x60)	260ml with disc cover (φ75x65)	360mlwith buckle cap(φ80x100)	790mlwith buckle cap(φ80x200)	
5mlwith inner convex cap(φ15x70)	130ml with disc cover (φ70x50)	270ml with disc cover (φ90x60)	420ml with disc cover (φ70x145)	860ml with disc cover (φ140x70)	
6mlwith buckle cap(φ16x50)	163ml with disc cover (φ90x35)	270mlwith buckle cap(φ90x60)	560ml with disc cover (φ115x70)	900mlwith disc cover(φ110x120)	
0.7ml with disc cap (φ20x4)	4ml with inner convex cap (φ14x45)	8ml with buckle cap (φ25x25)	1240ml with disc cover (φ125x125)	2500ml with disc cover (φ150x180)	
2ml with disc cap (φ30x5)	6.5ml with inner convex cap (φ19x35)	11ml with inner convex cap (φ19x58)	2700ml with disc cover (φ160x160)	2600ml with disc cover (φ130x245)	
3ml with disc cap (φ35x6)	7.5ml with inner convex cap (φ28x17)	15ml with buckle cap (φ30x30)	1290ml with disc cover (φ115x155)	3800ml with disc cover (φ160x240)	
3ml with outer buckle cap (φ35x6)	8ml with inner convex cap (φ25x25)	25ml with inner convex cap (φ28x58)	1460ml with disc cover (φ140x120)		
3ml with disc cap (φ20x18)	74ml with disc cover (φ45x65)	450ml with buckle cover (φ90x90)	630ml with disc cover (φ100x100)	1000ml with disc cover (φ115x130)	2400ml with inner convex cap (φ230x80)
21ml with inner convex cap (φ35x30)	95ml with disc cover (φ95x20)	470ml with disc cover (φ80x120)	840ml with disc cover (φ50x65)	1350ml with disc cover (φ125x150)	2600ml with disc cover (φ145x195)

21ml with buckle cap (Φ35x30)	100ml with disc cover (Φ60x55)	470ml with buckle cover (q80x120)	900ml with disc cover (Φ80x235)	1400ml with disc cover (Φ130x130)	3400ml with disc cover (Φ180x170)
39ml with inner convex cap (Φ35x58)	127ml with disc cover (Φ45x110)	480ml with disc cover (Φ95x95)	900ml with buckle cover (Φ80x235)	1600ml with disc cover (Φ140x140)	
39ml with buckle cap (Φ35x58)	450ml with disc cover (Φ90x90)	560ml with disc cover (Φ130x60)	950ml with disc cover (Φ120x120)	2000ml with disc cover (Φ150x140)	
73ml with buckle cap (Φ35x100)	100ml with disc cover (Φ58x60)	130ml with disc cover (Φ65x50)	160ml with disc cover (Φ65x65)	220ml with disc cover (Φ60x100)	275ml with disc cover (Φ60x120)
74ml with buckle cap (Φ45x65)	119ml with inner convex cap (Φ40x135)	140ml with disc cover (Φ115x20)	180ml with inner convex cap (Φ50x120)	230ml with disc cover (Φ100x40)	280ml with buckle cover (Φ80x80)
80ml with disc cover (Φ56x50)	120ml with buckle cap (Φ50x80)	145ml with inner convex cap (Φ50x100)	180ml with buckle cover (Φ50x120)	250ml with disc cover (Φ70x90)	300ml with buckle cover (Φ90x65)
85ml with buckle cap (Φ50x60)	127ml with buckle cover (Φ45x110)	145ml with buckle cap (Φ50x100)	185ml with disc cover (Φ59x87)	250ml with disc cover (Φ95x50)	310ml with disc cover (Φ70x100)
93ml with disc cap (Φ40x100)	130ml with disc cover (Φ60x60)	150ml with buckle cover (Φ90x30)	198ml with buckle cover (Φ85x50)	260ml with disc cover (Φ70x70)	375ml with disc cover (Φ70x120)
560ml(115x70)	900ml(110x120)	1100ml(107x160)	2600ml(130x245)		
610ml(80x155)	900ml(115x110)	1240ml(125x125)	2600ml(145x195)		
790ml(80x200)	950ml(120x120)	1290ml(115x155)	3800ml(160x240)		
860ml(140x70)	1000ml(104x155)	1460ml(140x120)	5200ml(185x240)		
900ml(80x235)	1050ml(150x80)	2000ml(150x140)			
2520ml(Φ200x100)	5200ml(Φ185x240)	5240ml(Φ200x200)			
50ml (Φ40x60)	330ml (Φ95x60)	790ml (Φ80x200)	1240ml (Φ125x125)	3800ml (Φ160x240)	
163ml (Φ90x35)	360ml (Φ80x100)	860ml (Φ140x70)	1290ml (Φ115x155)	5200ml (Φ185x240)	
220ml (Φ100x35)	420ml (Φ70x145)	900ml (Φ110x120)	1460ml (Φ140x120)	5240ml (Φ200x200)	
250ml (Φ85x60)	470ml (Φ80x120)	900ml (Φ115x110)	2500ml(Φ150x180)		
270ml (Φ90x60)	560ml (Φ115x70)	1050ml (Φ150x80)	2520ml (Φ200x100)		
300ml (Φ100x50)	610ml (Φ80x155)	1100ml (Φ100x180)	2600ml(Φ130x245)		
Customized Φ56x50mm without cover	Customized Φ56x50mm with cover				

Alumina (Al₂O₃) Ceramic Crucible Semicircle Boat With Lid

Item Number: KM-C03



Introduction

Crucibles are containers widely used for melting and processing various materials, and semicircular boat-shaped crucibles are suitable for special smelting and processing requirements. Their types and uses vary by material and shape.

[Learn More](#)

5ml(40x25x17mm)	17ml(55x35x22mm)	42ml(100x40x25mm)	97ml(250x40x19mm)	9ml with lid (100x20x15mm)
7ml(100x20x20mm)	18ml(80x30x16mm)	48ml(100x45x22mm)	110ml(100x65x30mm)	20ml with lid (100x30x20mm)
9ml(65x25x16mm)	20ml(100x30x20mm)	58ml(60x55x40mm)	1025ml(200x130x60mm)	30ml with lid (100x35x18mm)
9ml(100x20x15mm)	30ml(100x35x18mm)	60ml(150x40x20mm)	700ml(150x150x60mm)	40ml with lid (100x40x20mm)
9.5ml(38x34x19mm)	40ml(60x54x24mm)	65ml(100x50x30mm)	800ml(180x120x45mm)	42ml with lid (100x40x25mm)
12ml(40x35x25mm)	40ml(100x40x20mm)	85ml(115x55x28mm)	7ml with lid (100x20x20mm)	65ml with lid (100x50x30mm)
700ml with lid (150x150x60mm)				



Kintek Solution

Head Quarter: No.89 Science Avenue, High-Tech Zone,
Zhengzhou, China

Hongkong Office: 300 Lockhart Road, Wan Chai,
Hongkong

Canada Office: Boulevard Graham, Mont-Royal, QC, H3P
2C7, Canada

